

From the inventor of Leeb

equotipilive

Smart Portable Wireless Leeb Hardness Solution



Equotip[®] Leeb D Complete Portfolio

Equotip[®] Live

- Wireless •
- Real-time Data Sharing
- Cloud Backup •



Equotip® Piccolo / Bambino 2

Integrated •



Swiss Solutions since 1954

equotip[®] ive

The global industry standard reinvented



Measure

New generation wireless impact device and mobile app


✔ Find out more (Page 4)



Sync and share

Quick and easy data review and sharing





Following Proceq's known high quality standards and ensuring an accuracy of \pm 4 HL

Ultra portable wireless device perfect for confined spaces on-site

Multiple users can share same impact device / Use multiple impact devices with the same app



Developed for Challenging Environments

- IP 54 protected Equotip Live Leeb D Impact Device
- Special mobile covers and gloves to further increase protection

7.16

50 00 Stk

- Ultra portable solution with wireless connection
- Suitable for confined spaces

SA, am

01.)7.)6

eite: 2.045 ige: 5.990 Menge

am

.16

Equotip® App Hardness Testing Made Simple



User interface designed by experts for intuitive hardness testing




Hotspots: Predefined shortcuts for fast measuring and handling



Audio output of readings allow to keep mobile device in the pocket




On-screen help through measuring and settings steps





Equotip[®] App A New Measuring Experience





Globally accessible measuring data via live.proceq.com



Custom conversion curve options to increase accuracy on exotic materials



Verification and calibration information for increased reliability

Full traceability of data

Try out app: Download for free and review Proceq's training data set


Visit live.proceq.com for compatibility information






Swiss Solutions since 1954

Equotip[®] Live App Logbook for Full Control and Review



Proceq Live Sync

Fast and Secure Report Generation



+ Secure web platform live.proceq.com
 + Centralized report template and profile management
 + Full data traceability with continuous online backup to prevent data loss



Equotip® Live First Internet of Things (IoT) Hardness Testing Solution



Flexible budgeting

Initial set-up contribution and small monthly fee to preserve capital for your business

Unbeatable value for your hardness solution

Latest technology from the inventor of Leeb for a fraction of the cost



Predictable cost planning

110

Fixed fee to help you plan well in advance


Protect your investments

Use existing mobile devices to leverage your IoT and Industry 4.0 investments

Experience the Equotip[®] Live At your Place

- Get professional advice and helpful hints from our experienced experts
- Global network of Proceq subsidiaries and certified business partners
- Thousands of satisfied customers
 worldwide thanks to superior service


Proceq – A Story of Success





The Leeb Measuring Principle Invented by Proceq

Leeb hardness principle is based on the dynamic (rebound) method. An impact body with a hard metal test tip is propelled by spring force against the surface of the test piece. Surface deformation takes place when the impact body hits the test surface, which results in loss of kinetic energy. This energy loss is detected by a comparison of velocities v_i and v_r when the impact body is at a precise distance from the surface for both the impact and rebound phase of the test, respectively.



Velocities are measured using a permanent magnet in the impact body that generates an induction voltage in the coil which is precisely positioned in the impact device. The detected voltage is proportional to the velocity of the impact body. Signal processing is then providing the hardness reading.

			N. Contraction	
		Scales	Units	Range
	Steel and cast steel	Vickers Brinell Rockwell Shore Rm N/mm ²	HV HB HRB HRC HS o1 o2 o3	81-955 81-654 38-100 20-68 30-99 275-2194 616-1480 449-847
e	Cold work tool steel	Vickers Rockwell	HV HRC	80-900 21-67
Measuring Range	Stainless steel	Vickers Brinell Rockwell	HV HB HRB HRC	85-802 85-655 46-102 20-62
	Cast iron lamellar graphite GG	Brinell Vickers Rockwell	HB HV HRC	90-664 90-698 21-59
	Cast iron, nodular graphite GGG	Brinell Vickers Rockwell	HB HV HRC	95-686 96-724 21-60
	Cast aluminium alloys	Brinell Vickers Rockwell	HB HV HRB	19-164 22-193 24-85
	Copper/zinc alloys (brass)	Brinell Rockwell	HB HRB	40-173 14-95
	CuAI/CuSn-alloys (bronze)	Brinell	HB	60-290
	Wrought copper alloys, low alloyed	Brinell	HB	45-315
	» Other combinations possible through custom conversions			

Surface preparation	Roughness grade class ISO 1302		N7
	Max. roughness de	pth R, (µm / µinch)	10 / 400
	Average roughness	R _a (µm / µinch)	2 / 80
Minimum sample mass	Of compact shape	(kg / lbs)	5 / 11
	On solid support (k	g / lbs)	2/4.5
	Coupled on plate (k	(g / lbs)	0.05 / 0.2
Minimum sample thickness	Uncoupled (mm / ir	nch)	25 / 0.98
	Coupled (mm / inch)		3 / 0.12
	Surface layer thickness (mm / inch)		0.8 / 0.03
Indentation size on test surface	With 300 HV, 30 HRC	Diameter (mm / inch)	0.54 / 0.021
		Depth (µm / µinch)	24 / 960
	With 600 HV, 55 HRC	Diameter (mm / inch)	0.45 / 0.017
		Depth (µm / µinch)	17 / 680
	With 800 HV, 63 HRC	Diameter (mm / inch)	0.35 / 0.013
		Depth (µm / µinch)	10 / 400

Test Piece Requirements

Technical Specifications

Full Standard Compliance and Traceability

Measuring

Measuring range	100 - 1000 HLD
Measuring accuracy	± 4 HL (0.5 % at 800 HL)
Measuring resolution	1 HL / HV / HB 0.1 HRC / HRB / HS 1 N/mm² Rm
Impact direction	Automatic compensation (± 5°)
Storage temperature	-20 to 60° C (-4 to 140° F)
Operating temperature	-10 to 50°C (14 to 122°F)
Charging temperature	0 to 40° C (32 to 104° F)
Humidity	90% max.
IP rating	IP 54

General

Battery type	1x rechargeable AAA NiMH 1000 mAh
Operating hours	> 20 h continuously measuring (1 impact/5 sec)
Communication	USB 2.0, Bluetooth 4.0 Low Energy
Connector	Micro-USB B

ø 17.5 mm 46 mm (ø 0.69 in) (1.81 in) ++146 mm (5.74 in) 86 g (w/o battery) (3.03 oz) 24.5 mm (0.96 in)

Full Traceability

In combination with the Equotip Leeb test blocks, hardness testing with the Equotip Live solution is fully traceable.

ASTM	A956 / A370	ASTM
ISO	16859	Guidelines
DIN	50156 (withdrawn)	ASME CRTD-91 DGZfP Guideline
GB/T	17394	VDI / VDE Guideli Nordtest Technica
JB/T	9378	424-2, 424-3

Standards

Conversion Standard

TM E140

- MC 1
- line 2616 Paper 1 al Reports 421-1,

proce

Equotip® Live Leeb D

- 358 10 011 **Equotip Live Leeb D** consists of Equotip Live-Leeb D Basic Impact Device, Equotip Impact Body D/DC, support ring D6, micro-USB cable, cleaning brush, rechargeable AAA battery, documentation, carrying strap and carrying case. Includes Equotip Live Bluetooth module and full connectivity to mobile device. 2 year "Reporting Feature Equotip Live" included with the option to extend annually at any time (with associated fee).
- 358 10 012 **Equotip Live Rental Leeb D** consists of Equotip Live Leeb D Basic Impact Device, Equotip Impact Body D/DC, support ring D6, micro USB-Cable, cleaning brush, rechargeable AAA battery, documentation, carrying strap and carrying case. Includes Equotip Live Bluetooth module and full connectivity to mobile device. Additionally requires "Reporting Feature Equotip Live."
- 358 99 003 **Reporting Feature Equotip Live** consists of unlimited online storage, all reporting capabilities on mobile device and PC, and secure data backup solution and sharing features. Subscription ends automatically after 1 year without notice, unless renewed. Additionally requires "Equotip Live Leeb D," "Equotip Live Rental Leeb D," or "Equotip Live UCI HV1-HV10."

Service and Support

Proceq is committed to providing the best support and service available in the industry through the Proceq certified service centers worldwide. This results in a complete support for Equotip by means of our global service and support facilities.

Accessories		es
	358 00 101	Equotip Live Leeb D Impact Device Basic
	350 01 004	Equotip Impact Body D/DC
	358 01 340	Micro USB-Cable 0.5m (1.6 ft)
	350 01 015	Equotip coupling paste
	350 01 010	Equotip support ring D6a
	353 03 000	Set of support rings

Equotip Leeb Test Blocks Calibrated by Proceq

357 11 100	Equotip Test Block D/DC, <500 HLD / <220 HB
357 12 100	Equotip Test Block D/DC, ~600 HLD / ~325 HB
357 13 100	Equotip Test Block D/DC, ~775 HLD / ~56 HRC
357 13 105	Equotip Test Block D/DC, ~775 HLD, one side

Additional Test Block Calibrations

357 90 909	Equotip Leeb Test Block Additional Calibration HL (ISO 16859-3)
357 90 919	Equotip Leeb Test Block Additional Calibration HB (ISO 6506-3)
357 90 929	Equotip Leeb Test Block Additional Calibration HV (ISO 6507-3)
357 90 939	Equotip Leeb Test Block Additional Calibration HR (ISO 6508-3)

More accessories and test blocks are available. Please contact your local Proceq subsidiary for more information.

Warranty Information

Each instrument is backed by the standard Proceq warranty and extended warranty options.

- » Electronic portion of the instrument: 24 months
- » Mechanical portion of the instrument: 6 months

Subject to change without notice. All information contained in this documentation is presented in good faith and believed to be correct. Proceq SA makes no warranties and excludes all liability as to the completeness and/or accuracy of the information. For the use and application of any product manufactured and/or sold by Proceq SA explicit reference is made to the particular applicable operating instructions.





Click on the Proceq subsidiaries for more information





E-Shop USA

E-Shop Europe

E-Shop Asia



Globally organized seminars to help you learn more about our products and applications. Contact your local representative for further information.

Proceq SA Ringstrasse 2 8603 Schwerzenbach Switzerland 810 356 03E ver 04 2018 © Proceq SA, Switzerland. All rights reserved.



